EYEWASH STATIONS

FLASH FLOOD

Portable self-contained eyewash station, classified as a personal (secondary) eyewash device, provides flexible emergency eyewash capability in economical systems. Includes a 1-gallon container of *Eyesaline*[®] solution providing three full minutes of gravity fed flow. The protective nozzle covers are easily pulled off in an emergency and each nozzle has a built-in filter for extra protection.

SPERIAN

Model		Wt.
No.	Description	lbs.
SA419	FlashFlood eyewash station	14
SA403	Eyesaline® 1 gal. refills (4/pkg.)	36
SA420	Wire rack for cartridges	3
SA421	Replacement pull strap	1

PORTA-STREAM I & II

Self-contained high-impact polyethylene eyewash units mount on any wall or sit on a level surface. Single pull strap once activated, leaves workers hands free to hold eyes open. Available in 70-oz. or 180-oz. units. Each unit supplied with *Eyesaline* concentrate to mix with water. Optional dust cover available to keep flushing area free of contaminants. Removal of cover pulls off retainer caps and activates flow.



Model		Wt.
No.	Description	lbs.
SA425	Porta-Stream 1 - 6 gal., 6 min. flush	19
SA427*	Porta-Stream 2 - 16 gal., 15 min. flush	36
SA408	Eyesaline® concentrate, for (SA425) 70 oz.	5
SA411	Eyesaline® concentrate, for (SA427) 180 oz.	13
SA426	Replacement pull-strap (SA425,SA427)	1
SA412	Dust Cover (SA425, SA427)	1

^{*} SEI certified to meet ANSI Z358.1

PURE FLOW 1000™

- · Sure-grip handle provides instant, simple activation
- Activation straps display expiration date
- · Integral drain valve allows easy draining of reservoir after use
- Integral fluid reservoir captures waste fluid, eliminating potential safety hazards and simplifying fluid disposal
- Once activated, this device automatically displays a prominent, Warning Service Immediately notice on the front of the unit; new fluid cartridges
- must be installed
 Requires two 3.8 gal. Eyesaline®
- fluid cartridges (sold separately)

 Fluid cartridges have a 24-month shelf life
- Device must be mounted on a wall or other suitable vertical surface
- Comes complete with product registration card, operating manual, metal hanging bracket for installation and an emergency eye wash sign
- SEI certified to meet ANSI Z358.1 standard



SPERIAN

Model No.	Description	Wt. Ibs.
SD552	Eyewash station (English Instructions)	40
SAJ678	Eyewash station (French Instructions)	40
SD553	Fluid cartridges (2/pkg)	70

WALL MOUNTED EYEWASH UNIT

- · Includes 10" diameter corrosion-resistant stainless bowl with stainless steel cover
- Exposed pipes and wall bracket are protected with Bradtect™ safety yellow polyurethane coating to protect unit from corrosion
- Activated by a highly visible plastic push handle and stay-open ball valve
- Dust cover pops open when highly visible stainless steel push handle is activated
- Includes safety sign and inspection tag
- · Weight: 9 lbs.
- Meets ANSI Z358.1 Standards
- SEI Certified

Model No. SA438 MFG No. S19-220DC



EYEWASH STATIONS

Wall stations provide job site convenience and immediate accessibility. Visible with full emergency use instructions in front. Constructed of sturdy high-impact plastic. Available in single 16 oz. or double 32 oz. full squeeze bottles or with empty spout and eye cup bottle. Solution is sterile isotonic. Includes four predifiled holes for easy wall mounting. Empty spill spout and eye cup bottles available separately. Ideal for high eye hazard areas.

Model No.	Mfg. No.	Description NORTH	Size"
SINGL	E STATIO		
SAK725*	E/A3827	W/Empty 16 oz. Spill Spout and Eye Cup	11 x 14
SAK726*	E/A3832	Panel Only	11 x 14
SR370	E/A3840	W/32 oz. Squeeze Bottle	6 1/2 x 11
SR371	E/A3837	Panel Only	6 1/2 x 11
SD556	E/A3825	W/Empty 32 oz. Spill Spout and Eye Cup	14 x 17
SD557	E/A3830	Panel Only	14 x 17
DOUBI	E STATI	ONS	
SN702	E/A3841	W/2-32 oz. Squeeze Bottles	11 x 14
SR372	E/A3838	Panel Only	11 x 14
SR373*	E/A3826	W/2 Empty 32 oz. Spill Spout and Eye Cup	14 x 17
SR374*	E/A3831	Panel Only	14 x 17

REPLACEMENTS

SAK727	E/A3836	Empty 16 oz. Spill Spout and Eye Cup Bottle
YA094	E/A3835	Empty 32 oz. Spill Spout and Eye Cup Bottle
SAK728	E/1507AIS0	16 oz. Eyewash Solution

SN703 E/1507BISO 32 oz. Eyewash Solution SR375 E/1507CISO 4 litres Eyewash Solution











SN703 SR375

FAUCET EYEWASH STATIONS

SN702

- Chrome-plated brass faucet-mounted eyewash converts any faucet into an emergency eyewash station
- No special plumbing required, won't interfere with normal faucet operation
- Easy to operate, turn on water and pull out knob to activate eyewash
- Water pressure holds spring loaded valve open, leaving hands free
- Push in knob to turn off water to revert faucet to normal operation
- No tools required, complete with adapters
- Available for eyewash or eye/face wash

SA422



•			
Model No.	Mfg. No.	Description	Wt. Ibs.
SA422	0K-1	Eyewash Station	0.50
SA423	0K-2	Eye/Face Wash Station	0.75
SR376*	-	Replacement Dust Caps for SA422	-
SF620*	_	Replacement Dust Caps for SA423	_

^{*} Sold per each

OPTI-KLENS® AERATED EYEWASH STATION

- Delivers a direct spray of gentle aerated water to the eyes in the event of a chemical, acid or caustic splash to the face
- · Push paddle for easy activation
- Ball valve remains open until closed manually
- 10" stainless steel bowl
- 1/2" IPS and 1 1/4" IPS drain
- · Softened flow heads with dust covers
- · Wall mount
- · Weight: 4 lbs.

Model No. SA402

